



Wire Management Products, Special Purpose Splicing Grip, Flexible Tube, 24" Mesh Length, Steel, 0.75-0.99"

By Bryant
Catalog # [FTD07524](#)

Wire Management Products, Special Purpose Splicing Grip, Flexible Tube, 24" Mesh Length, Steel, 0.75-0.99"



Features

- Flexible Tube
- 24" Mesh Length
- Steel
- 0.75-0.99"

Application

Cable and Wire Splicing

Specifications

EU RoHS Indicator No

Conductor

Number Of Conductors 1
Cable Diameter Range 0.75 in-0.99 in

Force Related

Approx Breaking Strength 6,800 lb.

General

Material - Mounting Hardware	On Cable Ends
Type	Tube
Series	Splicing Grips
OEM Brand Name	Hubbell Bryant
Material	Steel, Galvanized
UPC	781786241725
Style	Closed Mesh, Double Weave

Logistics

Carton Quantity 2

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)