



Wire Management Products, Special Purpose Splicing Grip, Flexible Tube, 24" Mesh Length, Steel, 1.00-1.49"

By Bryant
Catalog # [FTD10024](#)

Wire Management Products, Special Purpose Splicing Grip, Flexible Tube, 24" Mesh Length, Steel, 1.00-1.49"



Features

- Flexible Tube
- 24" Mesh Length
- Steel
- 1.00-1.49"

Application

Cable and Wire Splicing

Specifications

EU RoHS Indicator No

Conductor

Number Of Conductors 1
Cable Diameter Range 1-1.49 in

Force Related

Approx Breaking Strength 9,000 lb.

General

Material - Mounting Hardware	On Cable Ends
Type	Tube
Series	Splicing Grips
OEM Brand Name	Hubbell Bryant
Material	Steel, Galvanized
UPC	781786241800
Style	Closed Mesh, Double Weave

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)