



Power Protection Products, GFCI
Linecords, Commercial, Auto Set, 15A 125V
AC, 5-15R, 2' Cord Length, 4-6 mA Trip
Level, Yellow

By Bryant
Catalog # [GFCI15125A](#)

Power Protection Products, GFCI Linecords, Commercial, Auto
Set, 15A 125V AC, 5-15R, 2' Cord Length, 4-6 mA Trip Level,
Yellow

Features

- Commercial
- Auto Set
- 15A 125V AC
- 5-15R
- 2' Cord Length

Application

GFCI Line Cords

Specifications

EU RoHS Indicator Yes

Conductor

Strands Multi
Number Of Conductors 3
Conductor Size #14 AWG
Conductor Type Copper

Current

Current Rating 15 A
Amperage Rating 15 A
Voltage Rating Description 120 VAC
Current / Amperage Rating 15 A
Connectivity Plug-In
Voltage Rating 120 VAC



Dimensions

Outside Diameter 0.35

General

Series Commercial
OEM Brand Name Hubbell Bryant
Style Automatic Set
Color Black, Yellow
Item Type Industrial/Commercial Grade
Construction Fabricated
Type Line Cord
Material - Jacket PVC
Material - Insulation Elastomer
UPC 781786450066

Logistics

Carton Quantity 5

Operational

Temperature Rating -35 Degrees C to 66 Degrees C
 (-30 Degrees F to 150 Degrees F)

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)