



# Triple Tap Portable Inline GFCI, Manual Set, 15A, 120V AC, 2' - 12/3 SJTW

By Bryant  
Catalog # [GFCIST15125TRIM](#)

Manual Set, 15A, 120V AC, 2' - 12/3 SJTW



## Features

- High impact UV stabilized housing for long life
- All-glass circuit board provides moisture immunity
- Watertight GFCI housing for use in harsh environments
- Open neutral protection Trips upon loss of neutral
- Self-test functionality in accordance with UL 943

## Application

Outdoor/Indoor

## Specifications

|                          |           |
|--------------------------|-----------|
| Industry Standard(s)     | cULus 943 |
| Environmental Conditions | NEMA 3R   |
| Nema Rating              | 5-15      |

## Conductor

|                 |   |
|-----------------|---|
| Number Of Wires | 3 |
| Number Of Poles | 2 |

## Current

|                 |        |
|-----------------|--------|
| Phase           | Single |
| Amperage Rating | 15 A   |
| Wattage         | 1800 W |
| Voltage Rating  | 120 V  |

## General

|          |                   |
|----------|-------------------|
| Type     | Portable GFCI     |
| Series   | GFCI              |
| Material | Polycarbonate     |
| UPC      | 783585694191      |
| Style    | Triple Tap Outlet |
| Color    | Black/Yellow      |

## Operational

|                    |                              |
|--------------------|------------------------------|
| Temperature Rating | -30°F (-35°C) - 150°F (66°C) |
|--------------------|------------------------------|

## Product Assets

[Installation Manual \[Spanish, French, English\]](#)