



Power Protection Products, GFCI
Linecords, Commercial, Auto Set, 15A 125V
AC, 5-15R, 15' Cord Length, 4-6 mA Trip
Level, Yellow

By Bryant
Catalog # [GFCL15A](#)

Power Protection Products, GFCI Linecords, Commercial, Auto
Set, 15A 125V AC, 5-15R, 15' Cord Length, 4-6 mA Trip Level,
Yellow

Features

- Commercial
- Auto Set
- 15A 125V AC
- 5-15R
- 15' Cord Length

Application

GFCI Line Cords

Specifications

EU RoHS Indicator	Yes
Nema Rating	5-15P

Conductor

Strands	Multi
Number Of Conductors	3
Conductor Size	#14 AWG
Conductor Type	Copper

Current

Current Rating	15 A
Amperage Rating	15 A
Voltage Rating Description	120 VAC
Current / Amperage Rating	15 A
Connectivity	Plug-In
Voltage Rating	120 VAC



Dimensions

Outside Diameter	0.35
Weight	1.6 lb.

General

Series	Commercial
OEM Brand Name	Hubbell Bryant
Style	Automatic Set
Color	Black
Item Type	Industrial/Commercial Grade
Construction	Fabricated
Type	Line Cord
Material - Jacket	PVC
Material - Insulation	Elastomer
UPC	781786615076

Logistics

Carton Quantity	10
-----------------	----

Operational

Temperature Rating	-35 Degrees C to 66 Degrees C (-30 Degrees F to 150 Degrees F)
--------------------	---

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)