



Triple Tap Outlet Portable GFCI Line Cord, Automatic Set, 15A, 120V AC, 2' - 12/3 SJEOW

By Bryant
Catalog # [GFCST2TRIA](#)

Automatic Set, 15A, 120V AC, 2' - 12/3 SJEOW



Features

- High impact UV stabilized housing for long life
- All-glass circuit board provides moisture immunity
- Watertight GFCI housing for use in harsh environments
- Open neutral protection Trips upon loss of neutral
- Self-test functionality in accordance with UL 943

Application

Outdoor/Indoor

Specifications

Industry Standard(s)	cULus 943
Environmental Conditions	NEMA 3R
Nema Rating	5-15

Conductor

Number Of Wires	3
Number Of Poles	2

Current

Phase	Single
Amperage Rating	15 A
Wattage	1800 W
Voltage Rating	120 V

General

Type	Portable GFCI
Series	GFCI Series
Material	Polycarbonate
UPC	783585694399
Style	Triple Tap Outlet
Color	Black/Yellow

Operational

Temperature Rating	-30°F (-35°C) - 150°F (66°C)
--------------------	------------------------------

Product Assets

[Installation Manual \[Spanish, French, English\]](#)