



Power Protection Products, GFCI Plugs, Commercial, Auto Set, 15A 125V AC, 5-15R, Plug Only, 4-6 mA Trip Level, Black

By Bryant
Catalog # [GFP15A](#)



Power Protection Products, GFCI Plugs, Commercial, Auto Set, 15A 125V AC, 5-15R, Plug Only, 4-6 mA Trip Level, Black

Features

- Commercial
- Auto Set
- 15A 125V AC
- 5-15R
- Plug Only

Application

Wired On GFCI Protection

Specifications

EU RoHS Indicator	Yes
Nema Rating	5-15P

Conductor

Strands	Multi
Number Of Conductors	3
Conductor Size	#14 AWG
Conductor Type	Copper

Current

Current Rating	15 A
Amperage Rating	15 A
Voltage Rating Description	125 V
Current / Amperage Rating	15 A
Connectivity	Plug-In, Wired On
Voltage Rating	125 V

Dimensions

Outside Diameter	0.35
Weight	0.35 lb.

General

Series	Commercial
OEM Brand Name	Hubbell Bryant
Style	Automatic Set
Color	Black
Item Type	Industrial/Commercial Grade
Construction	Fabricated
Type	Plugs
Material - Jacket	PVC
Material - Insulation	Elastomer
UPC	781786615014

Logistics

Carton Quantity	10
-----------------	----

Operational

Temperature Rating	-35 Degrees C to 66 Degrees C (-30 Degrees F to 150 Degrees F)
--------------------	---

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)