



Power Protection Products, GFCI
Receptacles, Self Test, IG, Tamper and
Weather Restant, Hospital Grade, 15A 125V,
2-Pole 3-Wire Grounding, 5-15R

By Bryant
Catalog # [GFST82BKIG](#)

Power Protection Products, GFCI Receptacles, Self Test, IG,
Tamper and Weather Restant, Hospital Grade, 15A 125V, 2-Pole 3-
Wire Grounding, 5-15R, Black

Features

- Self Test
- IG
- Tamper and Weather Restant
- Hospital Grade
- 15A 125V

Specifications

Nema Rating5-15R

Conductor

Number Of Wires3-Wire
Number Of Poles2-Pole

Current

Current / Amperage Rating15 A
Amperage Rating15 A



Voltage Rating Description125 V
Voltage Rating125 V

General

TypeHeavy Duty
SeriesHospital Grade
UPC781786150430
StyleTamper-Resistant, Weather
Resistant
ColorBlack

Logistics

Carton Quantity10

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Catalog Page \[English\]](#)