



Power Protection Products, GFCI
Receptacles, Self Test, Hospital Grade, 15A
125V, 2-Pole 3-Wire Grounding, 5-15R, Ivory

By Bryant
Catalog # [GFST82I](#)

Power Protection Products, GFCI Receptacles, Self Test, Hospital
Grade, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Ivory



Features

- Self Test
- Hospital Grade
- 15A 125V
- 2-Pole 3-Wire Grounding
- 5-15R

Specifications

Nema Rating5-20R

Conductor

Number Of Wires3-Wire
Number Of Poles2-Pole

Current

Current / Amperage Rating20 A
Amperage Rating20 A

Voltage Rating Description125 V
Voltage Rating125 V

General

TypeHeavy Duty
SeriesHospital Grade
UPC781786150133
StyleStandard
ColorIvory

Logistics

Carton Quantity10

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)