



Power Protection Products, GFCI
Receptacles, Self Test, IG, Tamper and
Weather Resistant, Hospital Grade, 15A
125V, 2-Pole 3-Wire Grounding, 5-15R

By Bryant
Catalog # [GFST82LAIG](#)

Power Protection Products, GFCI Receptacles, Self Test, IG,
Tamper and Weather Resistant, Hospital Grade, 15A 125V, 2-Pole
3-Wire Grounding, 5-15R, Light Almond



Features

- Self Test
- IG
- Tamper and Weather Resistant
- Hospital Grade
- 15A 125V

Specifications

Nema Rating5-15R

Conductor

Number Of Wires3-Wire
Number Of Poles2-Pole

Current

Current / Amperage Rating15 A
Amperage Rating15 A

Voltage Rating Description125 V
Voltage Rating125 V

General

TypeHeavy Duty
SeriesHospital Grade
UPC781786150478
StyleTamper-Resistant, Weather
Resistant
ColorLight Almond

Logistics

Carton Quantity10

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)