



Power Protection Products, GFCI
Receptacles, Self Test, Tamper and
Weather Resistant, Hospital Grade, 15A
125V, 2-Pole 3- Wire Grounding, 5-15R,
White

By Bryant
Catalog # [GFST82WIG](#)



Power Protection Products, GFCI Receptacles, Self Test, Tamper
and Weather Resistant, Hospital Grade, 15A 125V, 2-Pole 3- Wire
Grounding, 5-15R, White

Features

- Self Test
- Tamper and Weather Resistant
- Hospital Grade
- 15A 125V
- 2-Pole 3- Wire Grounding

Specifications

Nema Rating 5-15R

Conductor

Number Of Wires 3-Wire
Number Of Poles 2-Pole

Current

Current / Amperage Rating 15 A
Amperage Rating 15 A

Voltage Rating Description 125 V
Voltage Rating 125 V

General

Type Heavy Duty
Series Hospital Grade
UPC 781786150492
Style Tamper-Resistant, Weather
Resistant
Color White

Logistics

Carton Quantity 10

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Catalog Page \[English\]](#)