



Power Protection Products, GFCI
Receptacles, Self Test, IG, Tamper and
Weather Resistant, Hospital Grade, 20A
125V, 2- Pole3-Wire Grounding, 5-20R

By Bryant
Catalog # [GFST83GYIG](#)

Power Protection Products, GFCI Receptacles, Self Test, IG,
Tamper and Weather Resistant, Hospital Grade, 20A 125V, 2-
Pole3-Wire Grounding, 5-20R, Gray

Features

- Self Test
- IG
- Tamper and Weather Resistant
- Hospital Grade
- 20A 125V

Specifications

Nema Rating5-20R

Conductor

Number Of Wires3-Wire
Number Of Poles2-Pole

Current

Current / Amperage Rating20 A
Amperage Rating20 A



Voltage Rating Description125 V
Voltage Rating125 V

General

TypeHeavy Duty
SeriesHospital Grade
UPC781786150522
StyleTamper-Resistant, Weather
Resistant
ColorGray

Logistics

Carton Quantity10

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)