



20A COMM HG SELF TEST TR ALARM GFR GRAY

By Bryant
Catalog # [GFST83GYTRB](#)

20A COMM HG SELF TEST TR ALARM GFR GRAY



Features

- Self Test

Specifications

Nema Rating 5-20R

Conductor

Number Of Wires 3-Wire
Number Of Poles 2-Pole

Current

Current / Amperage Rating 20 A
Amperage Rating 20 A
Voltage Rating Description 125 V
Voltage Rating 125 V

General

Type Heavy Duty
Series Hospital Grade
UPC 781786390263
Style Tamper-Resistant
Color Gray

Logistics

Carton Quantity 25

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Catalog Page \[English\]](#)