



Power Protection Products, GFCI
Receptacles, Self Test, IG, Tamper and
Weather Resistant, Hospital Grade, 20A
125V, 2-Pole 3-Wire Grounding, 5-20R

By Bryant
Catalog # [GFST83IG](#)

Power Protection Products, GFCI Receptacles, Self Test, IG,
Tamper and Weather Resistant, Hospital Grade, 20A 125V, 2-Pole
3-Wire Grounding, 5-20R, Brown



Features

- Self Test
- IG
- Tamper and Weather Resistant
- Hospital Grade
- 20A 125V

Specifications

Nema Rating 5-20R

Conductor

Number Of Wires 3-Wire
Number Of Poles 2-Pole

Current

Current / Amperage Rating 20 A
Amperage Rating 20 A

Voltage Rating Description 125 V
Voltage Rating 125 V

General

Type Heavy Duty
Series Hospital Grade
UPC 781786150546
Style Tamper-Resistant, Weather
Resistant
Color Brown

Logistics

Carton Quantity 10

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)