



Power Protection Products, GFCI
Receptacles, Self Test, IG, Tamper and
Weather Resistant, Hospital Grade, 20A
125V, 2-Pole 3-Wire Grounding, 5-20R

By Bryant

Catalog # GFST83LAIG



Power Protection Products, GFCI Receptacles, Self Test, IG,
Tamper and Weather Resistant, Hospital Grade, 20A 125V, 2-Pole
3-Wire Grounding, 5-20R, Light Almond

Features

- Self Test
- IG
- Tamper and Weather Resistant
- Hospital Grade
- 20A 125V

Specifications

Nema Rating 5-20R

Conductor

Number Of Wires	3-Wire
Number Of Poles	2-Pole

Current

Current / Amperage Rating	20 A
Amperage Rating	20 A

Voltage Rating Description	125 V
Voltage Rating	125 V

General

Type	Heavy Duty
Series	Hospital Grade
UPC	781786150553
Style	Tamper-Resistant, Weather Resistant
Color	Light Almond

Logistics

Carton Quantity 10

Product Assets

[Catalog \[English\]](#)

[Catalog Page \[English\]](#)

[Catalog Page \[English\]](#)



A Hubbell brand