



Receptacle, 20A, Comm, HG, Self test,
Tamper Resistant, Alarm, GFR, Light
Almond

By Bryant
Catalog # [GFST83LATRB](#)

Receptacle, 20A, Comm, HG, Self test, Tamper Resistant, Alarm,
GFR, Light Almond



Features

- Comm
- HG
- Self test
- Tamper Resistant
- Alarm

Specifications

Nema Rating 5-20R

Conductor

Number Of Wires 3-Wire
Number Of Poles 2-Pole

Current

Current / Amperage Rating 20 A
Amperage Rating 20 A

Voltage Rating Description 125 V
Voltage Rating 125 V

General

Type Heavy Duty
Series Hospital Grade
UPC 781786390294
Style Tamper-Resistant
Color Light Almond

Logistics

Carton Quantity 25

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Catalog Page \[English\]](#)