




20A COMM HG SELF TEST TR ALARM GFR RED

By Bryant
Catalog # [GFST83RTRB](#)

20A COMM HG SELF TEST TR ALARM GFR RED



Features

- Self Test

Specifications

Nema Rating5-20R

Conductor

Number Of Wires3-Wire
Number Of Poles2-Pole

Current

Current / Amperage Rating20 A
Amperage Rating20 A
Voltage Rating Description125 V
Voltage Rating125 V

General

TypeHeavy Duty
SeriesHospital Grade
UPC781786390300
StyleTamper-Resistant
ColorRed

Logistics

Carton Quantity25

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Catalog Page \[English\]](#)