



Metal PlugTrak, 15A 1 Circuit, 10 Receptacle, 5' Length, Ivory

By Bryant
Catalog # [HBL20GB506IV](#)

Metal PlugTrak, 15A 1 Circuit, 10 Receptacle, 5' Length, Ivory



Features

- Multiple spacing configurations
- Gray or ivory scratch resistant finish
- Insulation displacement wiring provides superior wire retention

Performance

Electrical - Receptacle Rating - NEMA 5-15R and NEMA 5-20R,
Mechanical - Wire - #12 AWG Stranded Copper

Specifications

Industry Standard(s)	• CSA Standard C22.2 no. 62 • E253976 /E253830 /E253833 • UL Standard UL 5
EU RoHS Indicator	Contact Manufacturer

Conductor

Wire Size	#12 AWG THHN
-----------	--------------

Configuration

Number Of Receptacles	10
-----------------------	----

Current

Current / Amperage Rating	15 A
---------------------------	------

Dimensions

Length	5 ft
--------	------

General

Item Type	Pre-Wired PlugTrak
Type	Single Circuit
Series	Metal
Specifications	• Number of Receptacles - 10 Singles • PlugTrak Amperage - 15A • PlugTrak Length - 5 Foot • Receptacle Face - Thermoplastic • Spacing - 6 Inch OC • Wiring Type - Hard Wired
UPC	783585214566
Style	Standard
Color	Ivory

Logistics

Carton Quantity	2
-----------------	---

Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)