



PlugTrak, Steel, Tamper Resistant, 20A125V, 3' Length, Gray



By Bryant
Catalog # [HBL24GB306GYTR](#)

PlugTrak, Tamper Resistant 20A125V, 3'

Features

- Multiple spacing configurations
- Gray or ivory scratch resistant finish
- Insulation displacement wiring provides superior wire retention

Specifications

EU RoHS Indicator Contact Manufacturer

Configuration

Number Of Receptacles 6

Current

Current / Amperage Rating 20 A
Amperage Rating 20 A

Dimensions

Length 3 ft

General

Type Single Circuit
Series Metal
UPC 783585453064
Style Tamper Resistant
Color Gray

Logistics

Carton Quantity 2

Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)