



Bryant Wire and Cable Management,
Pulling Grip, Heavy Duty, Overhead Flexible
Eye, .50-.75"

By Bryant
Catalog # [MST050FE](#)

Bryant Wire and Cable Management, Pulling Grip, Heavy Duty,
Overhead Flexible Eye, .50-.75"



Features

- Heavy Duty
- Overhead Flexible Eye
- .50-.75"

Application

General Cable Pulling

Specifications

EU RoHS Indicator Yes

Conductor

Cable Diameter Range 0.50 in-0.74 in
Cable Specification UL Listed Circuit Wire
Cable Size .50-074" (1.27-1.88)

Force Related

Approx Breaking Strength	10,000 lb.
Load Capacity	2000
General	
Construction	Woven
Material - Mounting Hardware	Non-Mounted
Type	Flexible Eye
Series	Overhead Multiple Strength
OEM Brand Name	Hubbell Bryant
Material	Steel, Galvanized
UPC	781786282025
Style	Closed Mesh, Triple, Double, Single Weave

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)