



Bryant Wire and Cable Management, Pulling Grip, Heavy Duty, Overhead Flexible Eye, .75-.99"

By Bryant
Catalog # [MST075FE](#)

Bryant Wire and Cable Management, Pulling Grip, Heavy Duty,
Overhead Flexible Eye, .75-.99"



Features

- Heavy Duty
- Overhead Flexible Eye
- .75-.99"

Application

General Cable Pulling

Specifications

EU RoHS Indicator Yes

Conductor

Cable Diameter Range 0.75 in-0.99 in
Cable Specification UL Listed Circuit Wire
Cable Size .75-.99" (1.90-2.51)

Force Related

Approx Breaking Strength	14,400 lb.
Load Capacity	2880
General	
Construction	Woven
Material - Mounting Hardware	Non-Mounted
Type	Flexible Eye
Series	Overhead Multiple Strength
OEM Brand Name	Hubbell Bryant
Material	Steel, Galvanized
UPC	781786282049
Style	Closed Mesh, Triple, Double, Single Weave

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)