



Bryant Wire and Cable Management, Pulling Grip, Heavy Duty, Overhead Flexible Eye, 1.00-1.24"

By Bryant
Catalog # [MST100FE](#)

Bryant Wire and Cable Management, Pulling Grip, Heavy Duty,
Overhead Flexible Eye, 1.00-1.24"



Features

- Heavy Duty
- Overhead Flexible Eye
- 1.00-1.24"

Application

General Cable Pulling

Specifications

EU RoHS Indicator Yes

Conductor

Cable Diameter Range 1.00-1.24 in
Cable Specification UL Listed Circuit Wire
Cable Size 1.00-1.24" (2.54-3.15)

Force Related

Approx Breaking Strength	24,600 lb.
Load Capacity	4920
General	
Construction	Woven
Material - Mounting Hardware	Non-Mounted
Type	Flexible Eye
Series	Overhead Multiple Strength
OEM Brand Name	Hubbell Bryant
Material	Steel, Galvanized
UPC	781786282063
Style	Closed Mesh, Triple, Double, Single Weave

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)