



Bryant Wire and Cable Management, Pulling Grip, Heavy Duty, Overhead Flexible Eye, 1.50-1.74"

By Bryant
Catalog # [MST150FE](#)

Bryant Wire and Cable Management, Pulling Grip, Heavy Duty,
Overhead Flexible Eye, 1.50-1.74"



Features

- Heavy Duty
- Overhead Flexible Eye
- 1.50-1.74"

Application

General Cable Pulling

Specifications

EU RoHS Indicator Yes

Conductor

Cable Diameter Range 1.50 in-1.74 in
Cable Specification UL Listed Circuit Wire
Cable Size 1.50-1.74" (3.81-4.42)

Force Related

Approx Breaking Strength	30,600 lb.
Load Capacity	6120
General	
Construction	Woven
Material - Mounting Hardware	Non-Mounted
Type	Flexible Eye
Series	Overhead Multiple Strength
OEM Brand Name	Hubbell Bryant
Material	Steel, Galvanized
UPC	781786282100
Style	Closed Mesh, Triple, Double, Single Weave

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)