



Bryant Wire and Cable Management,
Pulling Grip, Heavy Duty, Overhead Flexible
Eye, 3.00-3.49"

By Bryant
Catalog # [MST300FE](#)

Bryant Wire and Cable Management, Pulling Grip, Heavy Duty,
Overhead Flexible Eye, 3.00-3.49"



Features

- Heavy Duty
- Overhead Flexible Eye
- 3.00-3.49"

Application

General Cable Pulling

Specifications

EU RoHS Indicator Yes

Conductor

Cable Diameter Range 3.00 in-3.49 in
Cable Specification UL Listed Circuit Wire
Cable Size 3.00-3.49" (7.62-8.86)

Force Related

Approx Breaking Strength	48,000 lb.
Load Capacity	9600
General	
Construction	Woven
Material - Mounting Hardware	Non-Mounted
Type	Flexible Eye
Series	Overhead Multiple Strength
OEM Brand Name	Hubbell Bryant
Material	Steel, Galvanized
UPC	781786282186
Style	Closed Mesh, Triple, Double, Single Weave

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)