



Bryant Wire and Cable Management, Pulling Grip, Light Duty, Flexible Eye, 1.00-1.24" Cable Range

By Bryant
Catalog # PA100

Bryant Wire and Cable Management, Pulling Grip, Light Duty, Flexible Eye, 1.00-1.24" Cable Range



Features

- Light Duty
- Flexible Eye
- 1.00-1.24" Cable Range

Application

General Cable Pulling

Specifications

EU RoHS Indicator Yes

Conductor

Cable Diameter Range 1.00 in-1.24 in
 Cable Specification UL Listed Circuit Wire
 Cable Size 1.00-1.24" (2.54-3.15)

Force Related

Approx Breaking Strength 5,300 lb.

Load Capacity 1060

General

Construction Woven
 Material - Mounting Hardware Non-Mounted
 Type Flexible Eye
 Series Light Duty Grip
 OEM Brand Name Hubbell Bryant
 Material Steel, Galvanized
 UPC 781786280502
 Style Closed Mesh, Single Weave

Logistics

Carton Quantity 10

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)