



Bryant Wire and Cable Management, Pulling Grip, Light Duty, Flexible Eye, 1.25-1.49" Cable Range

By Bryant
Catalog # PA125

Bryant Wire and Cable Management, Pulling Grip, Light Duty, Flexible Eye, 1.25-1.49" Cable Range



Features

- Light Duty
- Flexible Eye
- 1.25-1.49" Cable Range

Application

General Cable Pulling

Specifications

EU RoHS Indicator Yes

Conductor

Cable Diameter Range 1.25 in-1.49 in
 Cable Specification UL Listed Circuit Wire
 Cable Size 1.25-1.49" (3.17-3.78)

Force Related

Approx Breaking Strength 5,300 lb.
 Load Capacity 1060

General

Construction Woven
 Material - Mounting Hardware Non-Mounted
 Type Flexible Eye
 Series Light Duty Grip
 OEM Brand Name Hubbell Bryant
 Material Steel, Galvanized
 UPC 781786280526
 Style Closed Mesh, Single Weave

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)