



# Bryant Wire and Cable Management, Pulling Grip, Light Duty, Flexible Eye, 1.50-1.74" Cable Range

By Bryant  
Catalog # PA150



Bryant Wire and Cable Management, Pulling Grip, Light Duty, Flexible Eye, 1.50-1.74" Cable Range

## Features

- Light Duty
- Flexible Eye
- 1.50-1.74" Cable Range

## Application

General Cable Pulling

## General

Approx Breaking Strength	6,800 lbs
Catalog Number	PA150
Construction	Woven
EU RoHS Indicator	Yes
Load Capacity	1360
Material	Steel, Galvanized

Material - Mounting Hardware	Non-Mounted
Series	Light Duty Grip
Style	Closed Mesh, Single Weave
Type	Flexible Eye
UPC	781786280540

## Conductor Related

Cable Diameter Range	1.50 in-1.74 in
Cable Size	1.50-1.74" (3.81-4.42)
Cable Specification	UL Listed Circuit Wire

## Product Assets

- [Catalogs - Bryant Full Line Catalog](#)
- [Specifications - PA150 Specification Sheet English](#)
- [Specifications - PA150 Specification Sheet French](#)