



Bryant Wire and Cable Management, Pulling Grip, Light Duty, Flexible Eye, 3.00- 3.49" Cable Range

By Bryant
Catalog # [PA300](#)

Bryant Wire and Cable Management, Pulling Grip, Light Duty,
Flexible Eye, 3.00-3.49" Cable Range



Features

- Light Duty
- Flexible Eye
- 3.00-3.49" Cable Range

Application

General Cable Pulling

Specifications

EU RoHS Indicator Yes

Conductor

Cable Diameter Range 3.00 in-3.49 in
Cable Specification UL Listed Circuit Wire
Cable Size 3.00-3.49" (7.62-8.86)

Force Related

Approx Breaking Strength 14,700 lb.
Load Capacity 2940

General

Construction Woven
Material - Mounting Hardware Non-Mounted
Type Flexible Eye
Series Light Duty Grip
OEM Brand Name Hubbell Bryant
Material Steel, Galvanized
UPC 781786280625
Style Closed Mesh, Single Weave

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)