



Bryant Wire and Cable Management, Pulling Grip, Underground Flexible Eye, .50-.61" Cable Range

By Bryant
Catalog # PH050

Bryant Wire and Cable Management, Pulling Grip, Underground Flexible Eye, .50-.61" Cable Range



Features

- Underground Flexible Eye
- .50-.61" Cable Range

Application

General Cable Pulling

Specifications

EU RoHS Indicator Yes

Conductor

Cable Diameter Range 0.50 in-0.61 in
 Cable Specification UL Listed Circuit Wire
 Cable Size .50-.61" (1.27-1.55)

Force Related

Approx Breaking Strength 4,500 lb.
 Load Capacity 900

General

Construction Woven
 Material - Mounting Hardware Non-Mounted
 Type Flexible Eye, Short Length
 Series Underground T-Type
 OEM Brand Name Hubbell Bryant
 Material Steel, Galvanized
 UPC 781786280267
 Style Closed Mesh, Double Weave

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)