



Bryant Wire and Cable Management, Pulling Grip, Underground Flexible Eye, .75-.99" Cable Range

By Bryant
Catalog # PH075

Bryant Wire and Cable Management, Pulling Grip, Underground Flexible Eye, .75-.99" Cable Range



Features

- Underground Flexible Eye
- .75-.99" Cable Range

Application

General Cable Pulling

Specifications

EU RoHS Indicator No

Conductor

Cable Diameter Range 0.75 in-0.99 in
 Cable Specification UL Listed Circuit Wire
 Cable Size .75-.99" (1.90-2.51)

Force Related

Approx Breaking Strength 6,800 lb.
 Load Capacity 1360

General

Construction Woven
 Material - Mounting Hardware Non-Mounted
 Type Flexible Eye, Short Length
 Series Underground T-Type
 OEM Brand Name Hubbell Bryant
 Material Steel, Galvanized
 UPC 781786280304
 Style Closed Mesh, Double Weave

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)