



Bryant Wire and Cable Management, Pulling Grip, Underground Flexible Eye, 1.00-1.49" Cable Range

By Bryant
Catalog # PH100

Bryant Wire and Cable Management, Pulling Grip, Underground Flexible Eye, 1.00-1.49" Cable Range



Features

- Underground Flexible Eye
- 1.00-1.49" Cable Range

Application

General Cable Pulling

Specifications

EU RoHS Indicator Yes

Conductor

Cable Diameter Range 1.00 in-1.49 in
 Cable Specification UL Listed Circuit Wire
 Cable Size 1.00-1.49" (2.54-3.78)

Force Related

Approx Breaking Strength 9,600 lb.
 Load Capacity 1920

General

Construction Woven
 Material - Mounting Hardware Non-Mounted
 Type Flexible Eye, Short Length
 Series Underground T-Type
 OEM Brand Name Hubbell Bryant
 Material Steel, Galvanized
 UPC 781786280328
 Style Closed Mesh, Double Weave

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)