



Bryant Wire and Cable Management,
Pulling Grip, Underground Flexible Eye,
3.00-3.49" Cable Range

By Bryant
Catalog # [PH300](#)

Bryant Wire and Cable Management, Pulling Grip, Underground
Flexible Eye, 3.00-3.49" Cable Range



Features

- Underground Flexible Eye
- 3.00-3.49" Cable Range

Application

General Cable Pulling

Specifications

EU RoHS Indicator Yes

Conductor

Cable Diameter Range 3.00 in-3.49 in
Cable Specification UL Listed Circuit Wire
Cable Size 3.00-3.49" (7.62-8.86)

Force Related

Approx Breaking Strength 24,500 lb.
Load Capacity 4900

General

Construction Woven
Material - Mounting Hardware Non-Mounted
Type Flexible Eye, Short Length
Series Underground T-Type
OEM Brand Name Hubbell Bryant
Material Steel, Galvanized
UPC 781786280403
Style Closed Mesh, Double Weave

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)