



Bryant Wire and Cable Management,
Pulling Grip, Underground Flexible Eye,
3.50-3.99" Cable Range

By Bryant
Catalog # [PH350](#)

Bryant Wire and Cable Management, Pulling Grip, Underground
Flexible Eye, 3.50-3.99" Cable Range



Features

- Underground Flexible Eye
- 3.50-3.99" Cable Range

Application

General Cable Pulling

Specifications

EU RoHS Indicator Yes

Conductor

Cable Diameter Range 3.50 in-3.99 in
Cable Specification UL Listed Circuit Wire
Cable Size 3.50-3.99" (8.89-10.13)

Force Related

Approx Breaking Strength	31,000 lb.
Load Capacity	6200
General	
Construction	Woven
Material - Mounting Hardware	Non-Mounted
Type	Flexible Eye, Short Length
Series	Underground T-Type
OEM Brand Name	Hubbell Bryant
Material	Steel, Galvanized
UPC	781786280427
Style	Closed Mesh, Double Weave

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)