



Bryant Wire and Cable Management, Pulling Grip, Underground Revolving Eye, .50-.61" Cable Range

By Bryant
Catalog # [PHS050](#)

Bryant Wire and Cable Management, Pulling Grip, Underground
Revolving Eye, .50-.61" Cable Range



Features

- Underground Revolving Eye
- .50-.61" Cable Range

Application

General Cable Pulling

Specifications

EU RoHS Indicator Yes

Conductor

Cable Diameter Range 0.50 in-0.61 in
Cable Specification UL Listed Circuit Wire
Cable Size .50-.61" (1.27-1.55)

Force Related

Approx Breaking Strength 4,800 lb.
Load Capacity 960

General

Construction Woven
Material - Mounting Hardware Non-Mounted
Type Revolving Eye, Short Length
Series Underground K-Type
OEM Brand Name Hubbell Bryant
Material Steel, Galvanized
UPC 781786280007
Style Closed Mesh, Double Weave

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)