



Bryant Wire and Cable Management,
Pulling Grip, Underground Revolving Eye,
.62-.74" Cable Range

By Bryant
Catalog # [PHS062](#)

Bryant Wire and Cable Management, Pulling Grip, Underground
Revolving Eye, .62-.74" Cable Range



Features

- Underground Revolving Eye
- .62-.74" Cable Range

Application

General Cable Pulling

Specifications

EU RoHS Indicator Yes

Conductor

Cable Diameter Range 0.62 in-0.74 in
Cable Specification UL Listed Circuit Wire
Cable Size .62-74" (1.57-1.88)

Force Related

Approx Breaking Strength 6,800 lb.
Load Capacity 1360

General

Construction Woven
Material - Mounting Hardware Non-Mounted
Type Revolving Eye, Short Length
Series Underground K-Type
OEM Brand Name Hubbell Bryant
Material Steel, Galvanized
UPC 781786280021
Style Closed Mesh, Double Weave

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)