



Bryant Wire and Cable Management, Pulling Grip, Underground Revolving Eye, 1.00-1.49" Cable Range

By Bryant
Catalog # [PHS100](#)

Bryant Wire and Cable Management, Pulling Grip, Underground
Revolving Eye, 1.00-1.49" Cable Range



Features

- Underground Revolving Eye
- 1.00-1.49" Cable Range

Application

General Cable Pulling

Specifications

EU RoHS Indicator Yes

Conductor

Cable Diameter Range 1.00 in-1.49 in
Cable Specification UL Listed Circuit Wire
Cable Size 1.00-1.49" (2.54-3.78)

Force Related

Approx Breaking Strength 16,400 lb.
Load Capacity 3280

General

Construction Woven
Material - Mounting Hardware Non-Mounted
Type Revolving Eye, Standard Length
Series Underground K-Type
OEM Brand Name Hubbell Bryant
Material Steel, Galvanized
UPC 781786280069
Style Closed Mesh, Double Weave

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)