



Bryant Wire and Cable Management,
Pulling Grip, Underground Revolving Eye,
2.00-2.49" Cable Range

By Bryant
Catalog # [PHS200](#)

Bryant Wire and Cable Management, Pulling Grip, Underground
Revolving Eye, 2.00-2.49" Cable Range



Features

- Underground Revolving Eye
- 2.00-2.49" Cable Range

Application

General Cable Pulling

Specifications

EU RoHS Indicator Yes

Conductor

Cable Diameter Range 2.00 in-2.49 in
Cable Specification UL Listed Circuit Wire
Cable Size 2.00-2.49" (5.08-6.32)

Force Related

Approx Breaking Strength 27,200 lb.
Load Capacity 5440

General

Construction	Woven
Material - Mounting Hardware	Non-Mounted
Type	Revolving Eye, Standard Length
Series	Underground K-Type
OEM Brand Name	Hubbell Bryant
Material	Steel, Galvanized
UPC	781786280106
Style	Closed Mesh, Double Weave

Logistics

Carton Quantity 6

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)