



Bryant Wire and Cable Management,
Pulling Grip, Underground Revolving Eye,
4.50-4.99" Cable Range

By Bryant
Catalog # [PHS450](#)

Bryant Wire and Cable Management, Pulling Grip, Underground
Revolving Eye, 4.50-4.99" Cable Range



Features

- Underground Revolving Eye
- 4.50-4.99" Cable Range

Application

General Cable Pulling

Specifications

EU RoHS Indicator Yes

Conductor

Cable Diameter Range 4.50 in-4.99 in
Cable Specification UL Listed Circuit Wire
Cable Size 4.50-4.99" (11.43-12.67)

Force Related

Approx Breaking Strength 48,000 lb.
Load Capacity 9600

General

Construction Woven
Material - Mounting Hardware Non-Mounted
Type Revolving Eye, Standard Length
Series Underground K-Type
OEM Brand Name Hubbell Bryant
Material Steel, Galvanized
UPC 781786280205
Style Closed Mesh, Double Weave

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)