



Bryant Wire and Cable Management,
Pulling Grip, Underground Revolving Eye,
6.00-6.99" Cable Range

By Bryant
Catalog # [PHS600](#)

Bryant Wire and Cable Management, Pulling Grip, Underground
Revolving Eye, 6.00-6.99" Cable Range



Features

- Underground Revolving Eye
- 6.00-6.99" Cable Range

Application

General Cable Pulling

Specifications

EU RoHS Indicator Yes

Conductor

Cable Diameter Range 6.00 in-6.99 in
Cable Specification UL Listed Circuit Wire
Cable Size 6.00-6.99" (15.24-17.75)

Force Related

Approx Breaking Strength 54,000 lb.
Load Capacity 10800

General

Construction Woven
Material - Mounting Hardware Non-Mounted
Type Revolving Eye, Standard Length
Series Underground K-Type
OEM Brand Name Hubbell Bryant
Material Steel, Galvanized
UPC 781786280243
Style Closed Mesh, Double Weave

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)