



Bryant, Wire and Cable Management, Pulling Grip, Slack Mesh, Single Eye, 1.00-1.24" Cable Range

By Bryant
Catalog # [SCD100](#)

Bryant, Wire and Cable Management, Pulling Grip, Slack Mesh, Single Eye, 1.00-1.24" Cable Range



Features

- Slack Mesh
- Single Eye
- 1.00-1.24" Cable Range

Application

General Cable Pulling

Specifications

EU RoHS Indicator Yes

Conductor

Cable Diameter Range 1.00 in-1.24 in
Cable Specification UL Listed Circuit Wire
Cable Size 1.00-1.24" (2.54-3.15)

Force Related

Approx Breaking Strength 4,000 lb.

Load Capacity 800

General

Construction Woven
Material - Mounting Hardware Non-Mounted
Type Offset Eye
Series Slack Grip
OEM Brand Name Hubbell Bryant
Material Steel, Galvanized
UPC 781786271524
Style Closed Mesh, Double Weave

Logistics

Carton Quantity 2

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)