



Wire and Cable Management, Support  
Grips, Heavy Duty, Single Eye, Tin-Coated  
Bronze, 1.00-1.24"

By Bryant  
Catalog # SHC100U

Wire and Cable Management, Support Grips, Heavy Duty, Single  
Eye, Tin-Coated Bronze, 1.00-1.24"

Features

- Heavy Duty
- Single Eye
- Tin-Coated Bronze
- 1.00-1.24"

Application

Single Eye

Specifications

EU RoHS Indicator                      No

Conductor

Cable Diameter Range                1-1.24 in  
Cable Size                                1.00-1.24" (2.54-3.15)

Force Related



|                              |                           |
|------------------------------|---------------------------|
| Approx Breaking Strength     | 4,280 lb.                 |
| General                      |                           |
| Construction                 | Woven                     |
| Material - Mounting Hardware | Screw Hook or Beam Clamp  |
| Type                         | Single Eye                |
| Series                       | Heavy Duty                |
| OEM Brand Name               | Hubbell Bryant            |
| Material                     | Bronze, Tin Coated        |
| UPC                          | 781786244443              |
| Style                        | Closed Mesh, Double Weave |

Logistics

Carton Quantity                        5

Product Assets

[Catalog \[English\]](#)  
[Catalog Page \[English\]](#)