



Wire and Cable Management, Support Grips, Heavy Duty, Single Eye, Tin-Coated Bronze, 1.25-1.49"

By Bryant
Catalog # SHC125U

Wire and Cable Management, Support Grips, Heavy Duty, Single Eye, Tin-Coated Bronze, 1.25-1.49"

Features

- Heavy Duty
- Single Eye
- Tin-Coated Bronze
- 1.25-1.49"

Application

Single Eye

Specifications

EU RoHS Indicator No

Conductor

Cable Diameter Range 1.25 in-1.49 in
Cable Size 1.25-1.49" (3.17-.378)

Force Related



Approx Breaking Strength	4,280 lb.
General	
Construction	Woven
Material - Mounting Hardware	Screw Hook or Beam Clamp
Type	Single Eye
Series	Heavy Duty
OEM Brand Name	Hubbell Bryant
Material	Bronze, Tin Coated
UPC	781786244467
Style	Closed Mesh, Double Weave

Logistics

Carton Quantity 5

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)