



Circuit Watch Surge Suppression Straight Blade Receptacle, Industrial/Commercial Grade, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Brown

By Bryant
Catalog # [SP52A](#)

Circuit Watch Surge Suppression Straight Blade Receptacle,
Industrial/Commercial Grade, 15A 125V, 2-Pole 3-Wire Grounding,
5-15R, Brown



Features

- 15A 125V
- 2-Pole 3-Wire Grounding
- 5-15R
- Brown

Application

Duplex with Light and Alarm

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No
Nema Rating	5-15R

Current

Frequency Rating	60 Hz
Amperage Rating	15 A
Voltage Rating Description	125 V
Current Rating	15 A
Voltage Rating	125 V
Connectivity	Terminal Screws
Phase	Single Phase
Current / Amperage Rating	15 A

Dimensions

Display Size	Standard
General	
Color	Blue
Style	Surge Protection Only
Outlet	Straight Blade
Series	Specification Grade
OEM Brand Name	Hubbell Bryant
UPC	781786139008
Type	Duplex Receptacle
Material - Mounting Hardware	Mounting Screws
Item Type	Surge Protection Receptacles
Material	Composite

Logistics

Carton Quantity	10
-----------------	----

Operational

Response Time	5
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)
Indicator(s) Type	LED and Audible Alarm

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)