



Circuit Watch Surge Suppression Straight Blade Receptacle, Industrial/Commercial Grade, Isolated Ground, 15A 125V, 2- Pole 3-Wire Grounding, 5-15R

By Bryant
Catalog # [SP52IGIA](#)

Circuit Watch Surge Suppression Straight Blade Receptacle,
Industrial/Commercial Grade, Isolated Ground, 15A 125V, 2- Pole
3-Wire Grounding, 5-15R, Ivory



Features

- Isolated Ground
- 15A 125V
- 2- Pole 3-Wire Grounding
- 5-15R
- Ivory

Application

IG Duplex with Light and Alarm

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No
Nema Rating	5-15R

Current

Current Rating	15 A
Amperage Rating	15 A
Frequency Rating	60 Hz
Voltage Rating Description	125 V
Phase	Single Phase
Current / Amperage Rating	15 A
Connectivity	Terminal Screws
Voltage Rating	125 V

Dimensions

Display Size	Standard
General	
Series	Specification Grade
OEM Brand Name	Hubbell Bryant
Outlet	Straight Blade
Style	Isolated Ground
Color	Ivory
Item Type	Surge Protection Receptacles
Material - Mounting Hardware	Mounting Screws
Type	Duplex Receptacle
Material	Composite
UPC	781786139121
Logistics	
Carton Quantity	10
Operational	
Response Time	5
Indicator(s) Type	LED and Audible Alarm
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)