



# Circuit Watch Surge Suppression Straight Blade Receptacle, Hospital Grade, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Brown

By Bryant  
Catalog # [SP82A](#)

Circuit Watch Surge Suppression Straight Blade Receptacle,  
Hospital Grade, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Brown



## Features

- 15A 125V
- 2-Pole 3-Wire Grounding
- 5-15R
- Brown

## Application

Duplex with Light and Alarm

## Specifications

|                          |                                                 |
|--------------------------|-------------------------------------------------|
| Environmental Conditions | Indoor Dry Unless Protected By Additional Means |
| EU RoHS Indicator        | No                                              |
| Nema Rating              | 5-15R                                           |

## Current

|                            |                 |
|----------------------------|-----------------|
| Frequency Rating           | 60 Hz           |
| Amperage Rating            | 15 A            |
| Voltage Rating Description | 125 V           |
| Current Rating             | 15 A            |
| Voltage Rating             | 125 V           |
| Connectivity               | Terminal Screws |
| Phase                      | Single Phase    |
| Current / Amperage Rating  | 15 A            |

## Dimensions

|                              |                                             |
|------------------------------|---------------------------------------------|
| Display Size                 | Standard                                    |
| <b>General</b>               |                                             |
| Color                        | Blue                                        |
| Style                        | Surge Protection Only                       |
| Outlet                       | Straight Blade                              |
| Series                       | Hospital Grade                              |
| OEM Brand Name               | Hubbell Bryant                              |
| UPC                          | 781786139220                                |
| Type                         | Duplex Receptacle                           |
| Material - Mounting Hardware | Mounting Screws                             |
| Item Type                    | Surge Protection Receptacles                |
| Material                     | Composite                                   |
| <b>Logistics</b>             |                                             |
| Carton Quantity              | 10                                          |
| <b>Operational</b>           |                                             |
| Response Time                | 5                                           |
| Operating Temperature        | 32 Deg F to 140 Deg F (0 Deg C to 60 Deg C) |
| Indicator(s) Type            | LED and Audible Alarm                       |

## Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)