



Circuit Watch Surge Suppression Straight Blade Receptacle, Hospital Grade, Isolated Ground, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Brown

By Bryant
Catalog # [SP82IGA](#)



Circuit Watch Surge Suppression Straight Blade Receptacle, Hospital Grade, Isolated Ground, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Brown

Features

- Isolated Ground
- 15A 125V
- 2-Pole 3-Wire Grounding
- 5-15R
- Brown

Application

IG Duplex with Light and Alarm

Specifications

Environmental Conditions Indoor Dry Unless Protected By Additional Means

EU RoHS Indicator No
Nema Rating 5-15R

Current

Current Rating 15 A
 Amperage Rating 15 A
 Frequency Rating 60 Hz
 Voltage Rating Description 125 V
 Phase Single Phase
 Current / Amperage Rating 15 A
 Connectivity Terminal Screws
 Voltage Rating 125 V

Dimensions

Display Size Standard

General

Series Hospital Grade
 OEM Brand Name Hubbell Bryant
 Outlet Straight Blade
 Style Isolated Ground
 Color Blue
 Item Type Surge Protection Receptacles
 Material - Mounting Hardware Mounting Screws
 Type Duplex Receptacle
 Material Composite
 UPC 781786154551

Logistics

Carton Quantity 10

Operational

Response Time 5
 Indicator(s) Type LED and Audible Alarm
 Operating Temperature 32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)