



# Circuit Watch Surge Suppression Straight Blade Receptacle, Hospital Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Ivory

By Bryant  
Catalog # [SP83IA](#)

Circuit Watch Surge Suppression Straight Blade Receptacle,  
Hospital Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Ivory



## Features

- 20A 125V
- 2-Pole 3-Wire Grounding
- 5-20R
- Ivory

## Application

Duplex with Light and Alarm

## Specifications

|                          |                                                 |
|--------------------------|-------------------------------------------------|
| Environmental Conditions | Indoor Dry Unless Protected By Additional Means |
| EU RoHS Indicator        | No                                              |
| Nema Rating              | 5-20R                                           |

## Current

|                            |                 |
|----------------------------|-----------------|
| Frequency Rating           | 60 Hz           |
| Amperage Rating            | 20 A            |
| Voltage Rating Description | 125 V           |
| Current Rating             | 20 A            |
| Voltage Rating             | 125 V           |
| Connectivity               | Terminal Screws |
| Phase                      | Single Phase    |
| Current / Amperage Rating  | 20 A            |

## Dimensions

|                              |                              |
|------------------------------|------------------------------|
| Display Size                 | Standard                     |
| <b>General</b>               |                              |
| Color                        | Ivory                        |
| Style                        | Isolated Ground              |
| Outlet                       | Straight Blade               |
| Series                       | Hospital Grade               |
| OEM Brand Name               | Hubbell Bryant               |
| UPC                          | 781786139275                 |
| Type                         | Duplex Receptacle            |
| Material - Mounting Hardware | Mounting Screws              |
| Item Type                    | Surge Protection Receptacles |
| Material                     | Composite                    |

## Logistics

|                 |    |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

## Operational

|                       |                                             |
|-----------------------|---------------------------------------------|
| Response Time         | 5                                           |
| Operating Temperature | 32 Deg F to 140 Deg F (0 Deg C to 60 Deg C) |
| Indicator(s) Type     | LED and Audible Alarm                       |

## Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)