



Wire and Cable Management, Support Grip, Offset Eye, Closed Mesh, Tin-Coated Bronze, 0.63-0.74"

By Bryant
Catalog # [SPC062SO](#)

Wire and Cable Management, Support Grip, Offset Eye, Closed Mesh, Tin-Coated Bronze, 0.63-0.74"



Features

- Offset Eye
- Closed Mesh
- Tin-Coated Bronze
- 0.63-0.74"

Application

Offset Eye

Specifications

EU RoHS Indicator Yes

Conductor

Cable Diameter Range 0.63 in-0.74 in
Cable Size .63-.74" (1.60-1.88)

Force Related

Approx Breaking Strength 750 lb.

General

Construction	Woven
Material - Mounting Hardware	Screw Hook or Beam Clamp
Type	Offset Eye
Series	Standard Duty Series
OEM Brand Name	Hubbell Bryant
Material	Bronze, Tin Coated
UPC	781786371491
Style	Closed Mesh, Single Weave

Logistics

Carton Quantity 5

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)