



Wire and Cable Management, Support Grip, Offset Eye, Closed Mesh, Tin-Coated Bronze, 1.00-1.24"

By Bryant
Catalog # [SPC100SO](#)

Wire and Cable Management, Support Grip, Offset Eye, Closed Mesh, Tin-Coated Bronze, 1.00-1.24"



Features

- Offset Eye
- Closed Mesh
- Tin-Coated Bronze
- 1.00-1.24"

Application

Offset Eye

Specifications

EU RoHS Indicator Yes

Conductor

Cable Diameter Range 1-1.24 in
Cable Size 1.00-1.24" (2.54-3.15)

Force Related

Approx Breaking Strength 1,500 lb.

General

Series Standard Duty Series
OEM Brand Name Hubbell Bryant
Style Closed Mesh, Single Weave
Construction Woven
Material - Mounting Hardware Screw Hook or Beam Clamp
Type Offset Eye
Material Bronze, Tin Coated
UPC 781786372344

Logistics

Carton Quantity 100

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)