



Wire and Cable Management, Support Grip, Offset Eye, Closed Mesh, Tin-Coated Bronze, 1.25-1.49"

By Bryant
Catalog # [SPC125SO](#)

Wire and Cable Management, Support Grip, Offset Eye, Closed Mesh, Tin-Coated Bronze, 1.25-1.49"



Features

- Offset Eye
- Closed Mesh
- Tin-Coated Bronze
- 1.25-1.49"

Application

Offset Eye

Specifications

EU RoHS Indicator Yes

Conductor

Cable Diameter Range 1.25 in-1.49 in
Cable Size 1.25-1.49" (3.17-3.78)

Force Related

Approx Breaking Strength 1,500 lb.

General

Construction Woven
Material - Mounting Hardware Screw Hook or Beam Clamp
Type Offset Eye
Series Standard Duty Series
OEM Brand Name Hubbell Bryant
Material Bronze, Tin Coated
UPC 781786372504
Style Closed Mesh, Single Weave

Logistics

Carton Quantity 100

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)